

# FIAL 4

## Dishwashing machine detergent



### DESCRIPTION

Alkaline liquid detergent for washing of crockery in dishwashing machines with controlled foam for extremely hard water. Protects metallic parts and circuits of the machine, avoiding build up of rust.

### FORM OF USE

Dose Fial 4 between 2 and 6 g/litre depending on hardness of water and its temperature, which is recommended be between 50°C and 65°C.

It can be introduced in the machine by hand or by automatic dosing system.

### TECHNICAL CHARACTERISTICS

Aspect: Liquid.  
Color: Reddish.  
Smell: Without fragrance  
pH(10%, water) : 12.6 – 13.7  
Density: 1.20 – 1.25 g /cc  
Active substance concentration: 30-35%

### COMPOSITION

Alcalis, sequestratings, phosphonates, polyacrilates.

### PRESENTATION

Plastic containers:

FORMAT	6Kg	12Kg	25Kg
CODE	003FI406	003FI412	003FI425

### SECURITY/TOXICOLOGY

Keep out of the reach of children.  
Causes severe burns. Wear suitable protective clothing, gloves and eye/face protection.

### ADDITIONAL INFORMATION

INDUSTRIAL PRODUCT. PROFESSIONAL USE.

*Commercial information. For the handle and employment of product, follow the indications of the label and the MSDS. To resolve any doubt, can contact with our Technical Department: [tecnico@dermo.com](mailto:tecnico@dermo.com). The valid version of this document is available only in the web [www.dermo.com](http://www.dermo.com).*

Revision: 005      Date: 17/03/21